




Things to consider when choosing your metal disintegrator

Select a table top large enough to handle your biggest work piece.

Note: Portable models 3-S, 2-S and 2-SB have no worktop.



STANDARD TABLE SIZES

Size 2-SA/2-DV

31"x 31"

(795 x 795mm)

Capacity: 2000 lb (956 kg

19"x 19"


(481 x 481mm)

Capacity:

1500 lb


(506 kg)












The arc-er head can be used with existing machinery



High-precision 'Q' Head

Unique "in-the-quill" head provides the pinpoint accuracy you need to 'surgically' remove the smaller tap and drill sizes. Precision bearings keep the powerful vibrating action under

Operates in any position. The head is 31/4" (82mm) diameter, hard chromed and precision ground. It has 9" (230mm) of vertical travel with rack and pinion movement. Equipped with Auto Stop Gauge and Amp Meter for precise control of cutting arc current. Works with any Electro Arc Disintegrator power unit.

TAP SIZE	DEPTH OF BROKEN TAP	DIAMETER OF DISINTRODE	AVERAGE TIME		
1/4-20	7/8 to 1"	.125	1 min.		
5/16-18	1 to 11/4"	.156	1½ min.		
7/16-14	3/4 to 11/4"	.225	2¼ min.		
1/2-13	1 to 15/8"	.250	4% min.		
5%-11	1¼ to 2½"	.312	7½ min.		
3/4-10	2½ to 2¾"	.375	18 min.		

*Choosing A Power Supply

To remove broken taps in one pass:

10 KVA up to 3/4" (19 mm)

15 KVA up to 1-1/4" (32 mm)

20 KVA* up to 2" (50 mm)

*with IQ Head only

2-SEQT
IQ
•
•
15"
36"

2-SA SERIES				2-DV SERIES			1-S SERIES				HK-6V SERIES					
2-SA	2-SAT	2-SAQ	2-SAQT	2-DV	2-DVT	2-DVQ	2-DVQT	1-SV	1-SVT	1-SVQ	1-SVQT	HK-6V	HK-6VT	HK-6VQ	НК-6VQТ	
ARC•ER	ARC•ER	IQ	IQ	ARC•ER	ARC•ER	IQ	IQ	ARC•ER	ARC•ER	IQ	IQ	ARC•ER	ARC•ER	IQ	IQ	
	•		•		•		•		•		•		•		•	
	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	
30"	30"	30"	30"	36"	36"	36"	36"	36"	36"	36"	36"	36"	36"	36"	36"	
50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	50"	